

VL1600 PROFILE

SUBJECT

New software release

OVERVIEW

Updated firmware for the following fixtures

Fixture	Version
VL1600 PROFILE	120722

The latest software can be download from the product page or our website www.VARI-LITE.com

RELEASE NOTES

- Added the gobo wheel offset to the open on the gobo wheel.
- Changed tilt encoder calibration for a full range of travel will automatically detect if it needs to set the new calibration on the first install.
- Changed the gobo wheel acceleration and speed to match 2600 better.
- Added edge to the "Recal Optics" control channel command.

Important Note:

- Vari-Lite Recommends as standard practice, when using PEGASUS, to always first perform a SCAN DEVICES prior to sending firmware. This ensures any devices present on the DMX line that are different from the fixture you are sending software will be muted. This prevents any possible interference during the upload process.

Know software issues:

- None

CONTACT INFORMATION

For more information on this technical notice or on Vari-Lite products, please contact your Authorized Vari-Lite Dealer or Vari-Lite customer service at 1.214.647.7880.